

## VRA Suction Regulator American Type Suction Regulator



VRA-701 (-760mmHg)



-400mmHg



-300mmHg



-160mmHg

### Inlet Adapter



- Ohmeda
- Ohio



- Chemetron



- AFNOR



- DIN



- DISS



- Kawasaki



- MK-IV



**Vacuum Outlet** -- can connect with various types of outlet adapter, and customized for your special requirement.

### Feature:

- The gauge is built-in within regulator body.
- Accurate suction control within  $\pm 5\%$ .
- Quick switch -760: Reg/Off/Full vacuum  
-400/-300/-160: Reg/Off vacuum
- Clear Analog Display in 2 1/2" pressure gauge.
- Constantly vacuum control.
- Nice outlook with durable plastic case.
- Large control knob for easy setting.
- Available in a variety of inlet adapters.

### Model & Specification

	-760mmHg	-400mmHg	-300mmHg	-160mmHg
w/o adapter	VRA-701	VRA-401	VRA-301	VRA-101
w/ Ohmeda	VRA-711	VRA-411	VRA-311	VRA-111
w/ MK IV	VRA-721	VRA-421	VRA-321	VRA-121
w/ PB	VRA-731	VRA-431	VRA-331	VRA-131
w/ AFNOR	VRA-741	VRA-441	VRA-341	VRA-141
w/ Kawasaki	VRA-751	VRA-451	VRA-351	VRA-151
w/ DISS	VRA-761	VRA-461	VRA-361	VRA-161
w/ DIN	VRA-771	VRA-471	VRA-371	VRA-171
w/ Barb adapter	VRA-781	VRA-481	VRA-381	VRA-181
w/ Chemetron	VRA-791	VRA-491	VRA-391	VRA-191

### Safety Trap



Safety Trap are recommended to use for protecting regulators and preventing accidental overflow.

#### Safety Trap Connection

- 1/8" Male NPT
- DISS Vac

### Suction Bottle



AC-SJ12  
Reusable 1200c.c.



AC-SJ20  
Reusable 2000c.c.

# VRF Suction Regulator

## French Type Suction Regulator



VRF-701 (-760mmHg)

### Feature:

- The gauge is built outside of regulator body.
- Accurate suction control within  $\pm 5\%$ .
- Simplified internal mechanical design for easy maintenance and clean.
- Quick switch for On/Off vacuum.
- Clear Analog Display in 2 1/2" pressure gauge.
- Nice outlook with durable plastic case.
- Large control knob for easy vacuum adjustment.
- Available in a variety of inlet adapters.



AC-SJ18  
Disposable 1800c.c.



AC-SJ30  
Disposable 3000c.c.



**Vacuum Outlet** -- can connect with various types of outlet adapter, and customized for your special requirement.

### Inlet Adapter

- Ohmeda
- Ohio
- Chemetron
- AFNOR
- DIN
- DISS
- Kawasaki
- MK-IV

### Model & Specification

	0-760mmHg	0-400mmHg
w/o adapter	VRF-701	VRF-401
w/ Ohmeda	VRF-711	VRF-411
w/ MK IV	VRF-721	VRF-421
w/ PB	VRF-731	VRF-431
w/ AFNOR	VRF-741	VRF-441
w/ Kawasaki	VRF-751	VRF-451
w/ DISS	VRF-761	VRF-461
w/ DIN	VRF-771	VRF-471
w/ Barb adapter	VRF-781	VRF-481
w/ Chemetron	VRF-791	VRF-491

### Safety Trap



Safety Trap are recommended to use for protecting regulators and preventing accidental overflow.

#### Safety Trap Connection

- 1/8" Male NPT
- DISS Vac

**NEW**

## DIGITAL SUCTION REGULATOR

Gentec is proud to announce the release of the all-new Digital Suction Regulator. While preserving the look-and-feel and usability of our original 2 1/2" gauge analog version, we provide the added convenience of an easy-to-read digital display (including a digital sweeping needle.)

Truly the best of both worlds!

### Agion®\* Antimicrobial Product Protection

The built-in long-lasting product protection prevents growth of microbes on the surface of the knobs. The antimicrobial product protection is based on non-volatile, naturally occurring silver.



**DIGITAL**

**ANALOG**

- Lightweight with durable ABS plastic casing
- Impact-resistant internal components
- Corrosion-free components and can be thoroughly flushed
- On/off cycle settings can be adjusted without opening the case
- Accuracy: +/-1% for digital; +/- 2% for analog
- Intermittent timing cycles: 16 seconds on, 8 seconds off. (timing can be adjusted)
- Suction traps and a variety of fittings & adapters are available
- Color-coding available
- 10 year warranty























\* Agion's silver antimicrobial has been certified for its material content, recyclability, and manufacturing characteristics. Cradle To Cradle Certified™ products meet established standards for human health, environmental health and recyclability. Cradle To Cradle Certified™ is a certification mark of MBDC.



**ORDERING MATRIX**

**Instructions:** Select the suction regulator, adapter, fitting, and color (if needed), then write the model number below.

STEPS:	1 Suction Regulator	2 Adapter	3 Fitting	4 Color (Optional)	Model Number
Example:	881VR-160	- OH	- T	- YL	= 881VR-160-OH-T-YL
Please Write Your Selection:	_____	+ _____	+ _____	+ _____	= _____

1 SUCTION REGULATORS	2 ADAPTERS	3 FITTINGS	4 COLORS (OPTIONAL)
 <p><b>881VR-160D</b>   <b>881VR-160</b> Continuous / Intermittent 0-160</p>	 <p><b>00</b>   <b>CH</b></p>	 <p><b>A</b>   <b>D</b></p>	<ul style="list-style-type: none"> <li> <i>Blank (White)</i></li> <li> <b>YL (Yellow)</b></li> <li> <b>BL (Blue)</b></li> <li> <b>RD (Red)</b></li> <li> <b>PL (Purple)</b></li> <li> <b>PC (Peach)</b></li> <li> <b>PK (Pink)</b></li> <li> <b>GY (Gray)</b></li> <li> <b>GN (Green)</b></li> <li> <b>BB (Baby Blue)</b></li> </ul>
 <p><b>881VR-300D</b>   <b>881VR-300</b> Continuous / Intermittent 0-300</p>	 <p><b>OH</b>   <b>DH</b></p>	 <p><b>B</b>   <b>C</b></p>	
 <p><b>882VR-300D</b>   <b>882VR-300</b> Continuous Only 0-300</p>	 <p><b>PB</b>   <b>DS</b></p>	 <p><b>T</b></p>	
 <p><b>882VR-760D</b>   <b>882VR-760</b> Continuous Only 0-760</p>	 <p><b>OQ</b>   <b>OE</b></p>	 <p><b>TD</b>   <b>TH</b></p>	

**ACCESSORIES**

 <p>Suction Trap w/ No Fitting on Top <b>880VT-0</b></p>	 <p>Suction Trap w/ Male Trap Fitting Only <b>880VT-1</b></p>	 <p>Suction Trap w/ DISS Female Nut &amp; Nipple <b>880VT-2</b></p>	 <p>Suction Trap w/ DISS Female Hand-Tight <b>880VT-3</b></p>	 <p>Suction Trap w/ Tubing Nipple <b>880VT-4</b></p>
 <p>Vacuum Adapter DISS to Hose Barb <b>DISSM-V-HCHK</b></p>	 <p>Extension Adapter 2-1/2" Long <b>EXTADPT-1/8</b></p>	 <p>Security Cable <b>FMS-2</b></p>		



4525 Edison Avenue, Chino CA 91710 USA  
TEL: 909.606.2726 FAX: 909.606.6485

[www.gentechealthcare.com](http://www.gentechealthcare.com)